## Rittal - The System.

Faster – better – everywhere.





## SK 3184.800 Blue e+ S wall-mounted cooling unit

State: 31/10/2025 (Source: rittal.com/com-en)



# SK 3184.800 - Blue e+ S wall-mounted cooling unit 0.3 kW - 1 kW

Blue e+ S cooling units with tried-and-tested Blue e+ technology are the world's most energy-efficient cooling units. This means they reduce the carbon footprint of your machines and systems. Available in a brand new design with a host of smart functions.

#### **Features**

Model No.	SK 3184.800
Design	wall-mounted
Benefits	Contributes to climate-neutral production with average energy
	savings of 75% and a reduced carbon footprint
	The use of R-513A refrigerant makes them more environmentally friendly
	Multi-voltage capabilities and country-specific approvals support global usability
	Smart, simple monitoring via IoT interface
	User-friendly operation with the Rittal Scan & Service app
Material	Sheet steel
General colour	RAL 7035
Colour	Enclosure: RAL 7035
	Louvred grille: RAL 7012
Supply includes	Assembly parts
	Fully wired ready for connection (plug-in terminal strip)
	Integral electric condensate evaporation
Options	For remote monitoring and networking of cooling units and chillers
	in the Blue e+ generation, please use the IoT interface (Model No.
	3124.300). Increase machine availability and process reliability with
	remote monitoring of device data, statuses and system messages.
Total cooling output to	Cooling output L35 L35/50 Hz: 1 kW
DIN EN 14511	Cooling output L35 L35/60 Hz: 1 kW
	Cooling output L35 L50/50 Hz: 0.6 kW
	Cooling output L35 L50/60 Hz: 0.6 kW

© Rittal 2025 2

### Features

Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz
Note	Please observe the mounting instructions.  By downloading the software, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these licence conditions.  Only suitable for use in semi-outdoor areas (see instructions for description)
Note on Model No.	Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V)
Rated power input	0.6 kW
Air throughput (unimpeded air flow)	External circuit: 680 m³/h Internal circuit: 680 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.4 Refrigeration factor L35 L35 (EER) 60 Hz: 2.4
Design	wall-mounted
Dimensions	Width: 400 mm Height: 950 mm Depth: 196 mm
Required mounting cut-out	Cut-out width: 383 mm Cut-out height: 929 mm
Protection category to IEC 60 529	Internal circuit IP 55
Protection category NEMA	UL Type 12 UL Type 3R
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.31 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.2 t
Temperature control	e+ controller (factory setting +35 °C)
Operating temperature range	-20 °C60 °C
Storage temperature range	-40 °C70 °C
Operating temperature range of refrigerant circuit (active)	3 °C60 °C

© Rittal 2025 3

## Features

Heat pipe operating temperature range	-20 °C45 °C
Setting range	20 °C50 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.42 kW Power consumption L35 L35/60 Hz: 0.42 kW Power consumption L35 L50/50 Hz: 0.48 kW Power consumption L35 L50/60 Hz: 0.48 kW
Permissible operating pressure (p. max.)	34 bar
Packs of	1 pc(s).
Net weight	26.5
Gross weight	31.5
Customs tariff number	84158200
EAN	4028177949973
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

## Approvals

Approvals	30 - KC Korea
	UL + C-UL (listed)
	UL + C-UL - FTTA
Explanations	Declaration of conformity
	Declaration of conformity - F-gas regulation

© Rittal 2025