Rittal – The System.

Faster - better - everywhere.





SK 3201.970 Toroidal transformer

State: 28/10/2025 (Source: rittal.com/com-en)



SK 3201.970 - Toroidal transformer Primary connection 115 V/400 V

For power supply to wall-mounted 230 V air/water heat exchangers. Available with 115 V or 400 V primary connection.

Features

Model No.	SK 3201.970
Product description	For the power supply of wall-mounted 230 V air/water heat exchangers. Available with 115 V or 400 V primary connection.
Technical specifications	Output 110 VA
	Voltage tolerance ±10%
	Primary connection 3500 mm long
	Secondary connection 1500 mm long
	For mounting on a 35 mm support rail EN 50 022
Supply includes	Toroidal transformer
	Assembly parts
Packs of	1 pc(s).
Snap-mounting to support rails TS 35	Yes
To fit Model No.	3363.X0X
	3364.X0X
	3214.100
	3214.700
	3215.100
	3215.700
Dimensions	Width: 105 mm
	Height: 123 mm
	Depth: 55 mm
Rated operating voltage	115 V (primary), 1~, 50 Hz/60 Hz
	230 V (secondary), 1~, 50 Hz/60 Hz
Net weight	2.1

© Rittal 2025

2

Features

Customs tariff number	85043121
EAN	4028177690233
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

Approvals

Certificates	EAC
Explanations	Declaration of conformity

© Rittal 2025 3