


# Rittal – The System.

Faster – better – everywhere.



## SK 3311.040 Connection hose

State: 08/05/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3311.040 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

## Features

|  |  |
|--|--|
| Model No.                                | SK 3311.040  |
| Material                                 | NBR (internal) with steel spiral and fabric inlay  |
| Design                                   | Rack cooling   |
| Length                                   | 1.8 m  |
| Water connections                        | G 1½" internal thread  |
| Operating temperature range              | -30 °C...70 °C   |
| Permissible operating pressure (p. max.) | 16 bar   |
| Packs of                                 | 2 pc(s).   |
| Net weight                               | 6.302 kg   |
| Gross weight                             | 6.779 kg   |
| Customs tariff number                    | 39173200   |
| ETIM 9                                   | EC002515   |
| ETIM 8                                   | EC002515   |
| ECLASS 8.0                               | 27180712   |
| Product description                      | SK connection hose, for water connection at the top and bottom, for LCP rack/Inline CW, L: 1800 mm |

# Tender text

Water connection kit top/bottom,

3311.040, for LCP CW

3311.130/230/260/530/540/560/148/238/268/548/538/568

3312.130/230/250/260/530/540/550/560/570 and

3313.130/230/250/260/530/540/550/560/570/238/268/548/538/568

3314.130/230/250/260/530/540/542/550/560/570/238/268/548/538/568

The water connection kit is used to realise the cooling water connection between the LCP and existing pipework.

Flexible hoses compensate any deviations in dimensions and at the same time decouple the LCP from the existing pipework.

Two removable half-shells permit individual shortening of the hoses.

Thanks to a hose length of 1.8 m, the media connection to the LCP can be realised either from the bottom (raised floor) or from the top.

Water connection kit top/bottom, supply includes:

Two hydraulic hoses (NBR), resistant against water and antifreeze mixtures

Embedded steel wire spiral

Internal diameter: DN 32

Length: 1800 mm

Operating pressure 16 bar at 30 °C

Temperature range: -30 °C to +70 °C

Connection on LCP side:

90° elbow, pressed, G 1½" union nut, flat seal, SW 52

Connection on pipework side:

Shell clamping mounted on hose, G 1½" union nut, flat seal, SW 55