Rittal – The System.

Faster – better – everywhere.



SK 3311.040

Connection hose

State: 07/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3311.040 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

Features

Model No.	SK 3311.040
Material	NBR (internal) with steel spiral and fabric inlay
Design	Rack cooling
Length	1.8 m
Water connections	G 1½" internal thread
Operating temperature range	-30 °C...70 °C
Permissible operating pressure (p. max.)	16 bar
Packs of	2 pc(s).
Net weight	6.302 kg
Gross weight	6.779 kg
Customs tariff number	39173200
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK connection hose, for water connection at the top and bottom, for LCP rack/Inline CW, L: 1800 mm

© Rittal 2026

Tender text

Water connection kit top/bottom,
3311.040, for LCP CW
3311.130/230/260/530/540/560/148/238/268/548/538/568
3312.130/230/250/260/530/540/550/560/570 and
3313.130/230/250/260/530/540/550/560/570/238/268/548/538/568
3314.130/230/250/260/530/540/542/550/560/570/238/268/548/538/568

The water connection kit is used to realise the cooling water connection between the LCP and existing pipework.
Flexible hoses compensate any deviations in dimensions and at the same time decouple the LCP from the existing pipework.
Two removable half-shells permit individual shortening of the hoses.

Thanks to a hose length of 1.8 m, the media connection to the LCP can be realised either from the bottom (raised floor) or from the top.

Water connection kit top/bottom, supply includes:
Two hydraulic hoses (NBR), resistant against water and antifreeze mixtures
Embedded steel wire spiral
Internal diameter: DN 32
Length: 1800 mm
Operating pressure 16 bar at 30 °C
Temperature range: -30 °C to +70 °C
Connection on LCP side:
90° elbow, pressed, G 1½" union nut, flat seal, SW 52
Connection on pipework side:
Shell clamping mounted on hose, G 1½" union nut, flat seal, SW 55

© Rittal 2026