



Rittal – The System.

Faster – better – everywhere.



SK 3235.450

EC speed control

State: 08/02/2026 (Source: rittal.com/com-en)



FRIEDHELM LOH GROUP

SK 3235.450 - EC speed control Sensor for speed control

NTC sensor for temperature-dependent speed control of EC fans to reduce noise and save energy.

Features

Model No.	SK 3235.450
Product description	NTC sensor for temperature-dependent speed control of EC fans to reduce noise and save energy. Activation and power supply via an EC fan-and-filter unit.
Technical specifications	Control characteristic: fixed setpoint at 35 °C, with linear control range between +35 °C (maximum speed 100%) and +20 °C (minimum speed 10%)
Supply includes	External sensor with connection cable (length 3 m)
Packs of	1 pc(s).
Speed	100 %
To fit Model No.	3240.500/.900 3241.500/.900 3243.500/.900 3244.500/.900 3245.xxx 3140.500 3140.510 3245.8x0
Operating temperature range	-25 °C...80 °C
Rated operating voltage	10 V - 12 V (DC)
IP protection category to IEC 60 529	IP 40
Net weight	0.2
Gross weight	0.202
Customs tariff number	85423190
EAN	4028177696617

Features

ETIM 9 EC000256

ETIM 8 EC000256

ECLASS 8.0 27142320

Approvals

Certificates EAC

Explanations Declaration of conformity
Declaration of conformity UK