Rittal – The System.

Faster – better – everywhere.



SK 3313.450
Liquid Cooling Package


State: 31/10/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3313.450 - Liquid Cooling Package

Ideal for cooling of small and medium-sized IT applications.







Features

Model No.	SK 3313.450
Design	DX
Benefits	Maximum energy efficiency due to EC fan technology and IT-based control Minimal pressure loss at the air end, which in turn minimises the power consumption of the fans Temperature monitoring and control With redundant temperature sensor integrated at the air end as standard Thanks to the speed-regulated compressor, the cooling output is ideally adapted to actual requirements Specific maintenance of the LCP DX due to separation of cooling and server racks
Applications	Ideal for IT cooling of small and medium-sized locations One or two racks can be cooled separately
Function principle	The LCP is designed for siting within a bayed enclosure suite. Hot air is drawn in from the aisle at the rear of the device, cooled by the high-capacity compact impellers, and blown back into the room or cold aisle after cooling. Absorbed thermal energy is emitted to the ambient air at the external condenser location, without heating up the installation room

© Rittal 2026

Features

Material	Sheet steel, spray-finished
Colour	RAL 7035
Options	Dehumidification and reheater Low-temperature/high-temperature condenser (-40 °C/+53 °C) Air filter
Design	Suite cooling
Monitoring	Direct connection of the unit via SNMP over Ethernet Integration into RiZone
Total cooling output/Number of fan modules	35 kW/3
Total cooling output	35 kW
Modulation range	8 - 35 kW
Air throughput (unimpeded air flow)	At 50 Hz: 9,900 m³/h
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 1,000 mm
To fit enclosure type	VX IT
Installation in bayed enclosure suite	Flush
Rated operating voltage	380 V - 480 V, 3~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 22.4 A
Max. cooling output	35 kW
Type of electrical connection	Connection clamp
Duty cycle	100 %
Cooling medium	Refrigerant
EC fan	Yes
SNMP card	Yes
Fans may be exchanged with the system operational	Yes

Features

Temperature control	Linear fan control Inverter-controlled compressor
Pre-fuse	Miniature circuit-breaker/fuse: 40 A
Operating temperature range	5 °C...35 °C
Noise level	At 50 Hz: 68 dB(A)
Protection category to IEC 60 529	IP 20
Packs of	1 pc(s).
Net weight	300 kg
Gross weight	320 kg
CRA risk class	Default (Low Risk)
Customs tariff number	84158200
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	LCP Inline DX, 35 kW, flush, RAL 7035, WHD: 600 x 2000 x 1000 mm, 380 – 480 V/3~/50 – 60 Hz

Approvals

Explanations	Declaration of conformity

Tender text

LCP Inline DX 35kW, 3313.450
WHD (mm) 600x2000x1000mm

IT-optimised design, providing ideal support for "front-to-back" air routing for the 482.6 mm (19") installations.

The unit is a direct evaporation (DX) split unit, to be connected to a remote condenser unit.

The unit is able to guarantee a cooling output of up to 35 kW with standard server enclosure dimensions, the lowest possible weight, and comprehensive possibilities for monitoring.
The LCP Inline DX is mounted on the side of the rack.
The warm server air is drawn in through a perforated rear door and the cooled air is blown back via a perforated door in front of the perforated doors of the server rack and is thus made available to the 482.6 mm (19") equipment once more.
The LCP Inline DX is closed up to the server rack at the front and rear and there forms a flush joint with the rack.

The unit is equipped with three EC fans, for maximum efficiency and minimum power consumption.
The flow characteristics of the heat exchanger are optimised for the lowest possible pressure losses on the air side. This minimises the energy consumption of the fans.

An integrated inverter with corresponding controller serves to regulate the speed of the installed compressor.
The presence of inverter compressor and a continuous control of the external unit fans permit to achieve a stepless adaptation of the cooling output, also in partial-load operation thus granting high precision of the airflow temperature to the servers.
Moreover they guarantee elevated energy consumption reduction with consequent reduction in operating costs.

Alongside the compressor, the refrigerant circuit of the LCP Inline DX comprises a liquid receiver, electronic expansion valve, refrigerant sight glass, optimised heat exchanger, high and low-pressure sensors, Schrader valves, filter dryer, non-return valve, high/low-pressure

© Rittal 2026

switch and shut-off devices.
The refrigerant connections and the electrical power connection to the unit can be realised from above or below.

The LCP Inline DX and the server rack remain separate from each other. This simplifies assembly and service work and excludes the need for unwanted access to the server rack for maintenance purposes.
Maintenance and service for all relevant components can be realised quickly and simply from front or rear, thanks to the optimised layout.
The fans can be exchanged quickly and at any time, even while the system is operational (hot swapping).
The fans are installed in the cold air section, which increases their service life.

Condensate management is integrated into the unit. Any condensate is collected in a collecting tray in the base and from there discharged to the outside via a hose.

Thanks to the integrated controller, the LCP Inline DX operates fully autonomously.
The setpoint is the server intake air temperature, which is automatically held constant at the set value.
Two sensors are present in each case for detection of the cold and warm air temperatures, providing for the appropriate redundancy.

Monitoring and alarm management for all physical parameters is realised via SNMP and Ethernet.
SNMP interface is directly integrated.

A display with operating keys is integrated on the front of the unit to display and set the physical parameters.

The external condenser is needed to operate the LCP Inline DX and has to be ordered separately.
The DX system consisting of LCP and remote condenser has to be filled in with refrigerant R410A Wall- or roof mounting of the remote condenser are possible

Installation and commissioning on site, laying of the refrigerant pipes, and evacuation and filling of the system with refrigerant are not included in the scope of supply and must be realised by correspondingly qualified persons.

© Rittal 2026

Technical specifications:
Useful cooling output:„
35 kW at 35 °C ambient temperature at place of installation of the condenser
Installed fans: 3
Air throughput: max.9000 m³/h
Intake temperature, set: 22 °C
Connection, liquid side: 16 mm
Connection, gas discharge side: 16 mm
Power supply:„400 V, 3~, N, PE, 50/ 60 Hz (voltage range 380-480 V)
Prefuse: 40A
Max. connected load: 14,60kW
Refrigerant: R410A
Connection length, max.: 60 m
Height difference (condenser higher/lower), max: 20/3 m
Dimensions (WxHxD): 600x2000x1000mm
Colour: RAL 7035
Integrated SNMP card for network connection

Option on application:
Dehumidification + heater
Air filter (G3) with monitoring
High temperature condenser (up to +53°C)
Low temperature condenser + winter kit (down to -40°C)

Needed accessories:
3311.370„
Air cooled condenser for 3313.450 (-20°C to +45°C)

© Rittal 2026