Rittal – The System.

Faster - better - everywhere.





SK 3244.740 Blue e+ filter fan

State: 24/11/2025 (Source: rittal.com/com-en)



SK 3244.740 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput $20-1,160~\text{m}^3/\text{h}$, protection category IP 54 as standard.







2

Features

Model No.	SK 3244.740
Design	wall-mounted
Product description	Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.
Benefits	Maximum air throughput via pleated filter included in the delivered state Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly
Material	Plastic
Colour	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Diagonal, three-phase motor

© Rittal 2025

Features

Air throughput, unimpeded airflow	At 50 Hz: 700 m³/h
(with chopped-fibre filter)	At 60 Hz: 770 m³/h
Air throughput, unimpeded airflow	At 50 Hz: 867 m³/h
(with pleated filter)	At 60 Hz: 910 m³/h
Air throughput with matching	At 50 Hz: 537 m³/h
outlet filter including chopped-fibre filter	At 60 Hz: 587 m³/h
Air throughput with matching	At 50 Hz: 720 m³/h
outlet filter including pleated filter	At 60 Hz: 745 m³/h
Rated operating voltage	400 V, 3~, 50 Hz/60 Hz
	460 V, 3~, 60 Hz
Power consumption Pel	At 50 Hz: 116.9 W
	At 60 Hz: 165.6 W
Rated current max.	At 50 Hz: 0.22 A
	At 60 Hz: 0.28 A
Dimensions	Width: 323 mm
	Height: 323 mm
	Depth: 156 mm
Installation depth	136 mm
Mounting cut-out	Cut-out width: 292 mm
	Cut-out height: 292 mm
IP protection category to IEC 60 529	IP 54 with chopped-fibre filter/pleated filter
	IP 55 with pleated filter and absorber mat
	IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter
	Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-proof hood
Note	With the filter fan 3237.XXX, electrical connection is made via two
	single wires (length approx. 300 mm) on the unit, for all other filter
	fans, a screwless spring terminal is used
Operating temperature range	-30 °C55 °C

© Rittal 2025 3

Features

At 50 Hz: 64 dB(A)
At 60 Hz: 66 dB(A)
1 pc(s).
4.6
4.82
84145915
4028177997875
EC000320
EC000320
27180716

Approvals

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025