


Rittal – The System.

Faster – better – everywhere.



SK 3245.600

TopTherm fan-and-filter units

State: 30/04/2024 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3245.600 - TopTherm fan-and-filter units EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20 - 900 m³/h, standard protection category IP 54.



Features

Model No.	SK 3245.600
Product description	EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3.
Colour	RAL 7035
Supply includes	Complete unit ready to install, including chopped-fibre filter mat
Fan	Diagonal, EC motor
Air throughput (unimpeded air flow)	At 50 Hz: 890 m³/h At 60 Hz: 890 m³/h
Air throughput with outlet filter including chopped-fibre filter mat (quantity x order number)	1 x 3243060: 630/630 m³/h 2 x 3243060: 770/770 m³/h
Rated operating voltage	200 V - 240 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 1.33 A At 60 Hz: 1.33 A
Power consumption Pel	At 50 Hz: 165 W At 60 Hz: 165 W
Dimensions	Width: 323 mm Height: 323 mm
Installation dimensions	Build depth: 25 mm Installation depth: 130.5 mm

Features

Mounting cut-out	Cut-out width: 292 mm Cut-out height: 292 mm
EMC version	Yes
Note	To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays
IP protection category to IEC 60529	IP51 with chopped-fibre filter IP56 with chopped-fibre filter and hose-proof hood
Protection category NEMA	Type 1, 12, 3, 3R with chopped-fibre filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Service life	59,000 h
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...70 °C
Noise level	At 50 Hz: 72 dB(A)
Packs of	1 pc(s).
Weight/pack	3.5 kg
Customs tariff number	84145915
EAN	4028177652491
ETIM 7.0	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3.

Air throughput (unimpeded air flow): 890/890 m³/h

Power consumption 50/60 Hz: 165 / 165 W

Rated power input 50/60 Hz: 1,33 / 1,33 A

Rated operating voltage: 200-240 V, 1~, 50/60 Hz

Diagonal fan: Diagonal, EC-Motor

Dimensions [WxH]: 323x323 mm

Installation depth: 130,5 mm

Build depth: 25 mm

Required mounting cut-out [WxH]: 292x292 mm

Operating temperature range: -25°C to +55°C

Storage temperature range: -25°C to +70°C

Colour: RAL 7035

Protection category IP to IEC 60 529:

IP 51 with fleece filter

IP 56 with fleece filter with hose-proof hood

Protection category NEMA:

Type 1, 12, 3, 3R with fleece filter with hose-proof hood

Noise level 50/60 Hz: 72 dB(A)

Service life 50/60 Hz: 59.000 h

Weight: 3,5 kg