


Rittal – The System.

Faster – better – everywhere.



SK 3303.130

Wall-mounted cooling units

State: 20/12/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3303.130 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.



Features

Model No.	SK 3303.130
Material	Sheet steel
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 500 W Cooling output L35 L35/60 Hz: 610 W Cooling output L35 L50/50 Hz: 280 W Cooling output L35 L50/60 Hz: 310 W
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 2.6 A At 60 Hz: 2.6 A
Start-up current max.	At 50 Hz: 5.1 A At 60 Hz: 6.4 A
Air throughput (unimpeded air flow)	External circuit: 345 m³/h Internal circuit: 310 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.4
Design	wall-mounted

Features

Dimensions	Width: 280 mm Height: 550 mm Depth: 210 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.17 kg Global Warming Potential (GWP): 1,430 CO2 equivalent (CO2e): 0.24 t
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 360 W Power consumption L35 L35/60 Hz: 380 W Power consumption L35 L50/50 Hz: 465 W Power consumption L35 L50/60 Hz: 490 W
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packs of	1 pc(s).
EAN	4028177610453
ECLASS 8.0	27180704

Approvals

Certificates	EAC Ex
Explanations	Declaration of conformity Declaration of conformity UK