
Rittal – The System.

Faster – better – everywhere.



SK 3311.030

Touchscreen display, colour

State: 19/11/2026 (Source: www.rittal.com/com-en)

SK 3311.030 - Touchscreen display, colour for LCP Rack/ Inline CW

All relevant operating parameters are displayed directly on the LCP display, to allow directly monitoring of key LCP functions and the implementation of settings.

Features

Model No.	SK 3311.030
Product description	The display offers the opportunity of directly monitoring key functions of the LCP, and implementing settings.
Supply includes	Touchscreen display, colour Connection cable Assembly parts
To fit Model No.	SK 3311.130/230/260/530/540/560/148/238/268/548/538/568 SK 3312.130/230/250/260/530/540/550/560/570 SK 3313.130/230/250/260/530/540/550/560/570/238/268/548/538/568 SK 3314.130/230/250/260/530/540/542/550/560/570
Packs of	1 pc(s).
Net weight	0.3 kg
Gross weight	0.373 kg
CRA risk class	Default (Low Risk)
Customs tariff number	85312040
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK Touchscreen display, colour, for LCP Rack/Inline CW 3311./3312./3313./3314.xxx

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK

Tender text

SK touchscreen display, colour
for LCP Rack/Inline CW
3311.130/230/260/530/540/560/148/238/268/548/538/568
3312.130/230/250/260/530/540/550/560/570 and
3313.130/230/250/260/530/540/550/560/570/238/268/548/538/568
3314.130/230/250/260/530/540/542/550/560/570

Touchscreen display:
Via the display the user can see all relevant operating parameters of the LCP directly.
The benefit is that the user can recognise at a glance the status of the device and react immediately if necessary.

The following parameters are shown on the display in different levels:

Display of cold air temperature routed to the 19" equipment
Display of hot air temperature dissipated from the 19" equipment
Cooling output
Cooling water inlet / return temperature
Cooling water flow rate
Position of the control valve
Overview of all parameters at a glance
Display of alarm and warning messages
Overview page with IP address of the device<(>,<)> software status and contact (may be entered individually)
Change of the set value of the cold air temperature in front of the 19" level may be carried out on the display (blocking possible, if required)

Touchscreen display, supply includes:
Touchscreen display, colour, with assembly parts
4,3" display, 480 x 272 pixels
Resistive touch
Type 280 cd/m²

© Rittal 2026

Operating temperature: -20°C to +70°C
Connection cable