

Rittal – The System.

Faster – better – everywhere.



SV 3559.000 Plate clamp

State: 13/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3559.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

Features

Model No.	SV 3559.000
Product description	For connecting laminated copper bars, no drilling required.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	34 x 10 mm
To fit busbars	40 x 10
To fit busbars	Busbar E-Cu
Packs of	3 pc(s).
Net weight	0.9 kg
Gross weight	0.926 kg
PCF per pack (cradle-to-gate)	3.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Product description	SV Plate clamp, for laminated copper bar, clamping area WH: 34x10 mm, for busbar WH: 40x10 mm

Approvals

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

Plate clamps

for E-CU busbars with 3 - 10 mm thickness.

For bar width: up to 40 mm

Clamping area for laminated copper bars: 34 x 10 mm

Tightening torque: 6 - 8 Nm

Material:

Sheet steel, zinc plated, passivated