

Rittal – The System.

Faster – better – everywhere.



AS 4050.435

Wiring duct cutter MC125

State: 04/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.435 - Wiring duct cutter MC125

For manual cutting of wiring ducts, with adjustable length end stop for the machined material. Anodised contact surface with laser-engraved calibration in millimetres and inches. Integral finger guard ensures safe machining. Intended for mounting on a workbench.



Features

Model No.	AS 4050.435
Product description	For manual cutting of wiring ducts, with adjustable length end stop for the machined material. Anodised contact surface with laser-engraved calibration in millimetres and inches. Integral finger guard ensures safe machining. Intended for mounting on a workbench.
Benefits	Enables inexpensive manual cutting of wiring ducts Easier for cutting wiring ducts to length compared to sawing by hand
Support area	Width: 1,332 mm Height: 798 mm Depth: 405 mm
Insertion height (max.)	28 mm
Machinable wall thickness of cable ducts (max.)	2.5 mm
Max. machinable width of cable duct	125 mm

Features

Machinable material	Plastic
Packs of	1 pc(s).
Net weight	14.3 kg
Gross weight	15.43 kg
Customs tariff number	84778095
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17139290
Product description	MC125 wiring duct cutter for manually cutting wiring ducts and their covers to length