Rittal – The System.

Faster – better – everywhere.



# VX 5301.518
# Castor module

State: 02/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# VX 5301.518 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

## Features

| | |
|---|---|
| Model No. | VX 5301.518 |
| Supply includes | 1 transport module with 2 castors<br>1 transport module with 2 castors, fixed<br>Assembly parts |
| Dimensions | Width: 756 mm<br>Height: 82.5 mm<br>Depth: 79 mm |
| Assembly instruction | The base area must be open at the mounting points |
| To fit | Enclosure type: VX: = 800 mm<br>Enclosure type: VX IT |
| Load capacity | Max. admissible load: Static 15,000 N<br>Max. admissible load: Dynamic 10,000 N |
| Note | The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground. |
| Packs of | 1 pc(s). |
| Net weight | 11.5 kg |
| Gross weight | 12.12 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002621 |
| ECLASS 8.0 | 27189262 |
| Product description | Castor module for VX IT, for W: 800 mm, for easy movement directly at the point of use, for mounting directly on the enclosure. |

## Tender text

Castor module for W: 800 mm
For easy movement on site, can be mounted directly on the IT rack.
Scope of delivery:
1 transport module with 2 castors
1 transport module with 2 baying clamps, fixed
Assembly parts

© Rittal 2026