

# Rittal – The System.

Faster – better – everywhere.



## VX 5302.154

## 482.6 mm (19") mounting angles, dynamic

State: 15/08/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5302.154 - 482.6 mm (19") mounting angles, dynamic for VX IT

Mounting angles, also for accommodating server system installation kits.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | VX 5302.154   |
| Design                   | for 482.6 mm (19") mounting angles, dynamic   |
| Product description      | Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design can directly accommodate all commercially available mounting kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings. |
| Benefits                 | Integral, bidirectional U labelling<br>Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling   |
| Technical specifications | Side punchings, round and square, on a U pitch pattern<br>Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components<br>482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E         |
| Applications             | For mounting a 482.6 mm (19") mounting level within the VX IT rack system   |
| Material                 | Sheet steel, 2.5 mm   |
| Surface finish           | Primed  |
| Colour                   | RAL 9005  |
| Supply includes          | Assembly parts  |
| Mounting position        | front   |
| Installation options     | Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected  |

# Features

|                               |  |
|-------------------------------|--|
| Assembly instruction          | To be combined with cross-member, depth stays or mounting bracket for attachment<br>Use of the different mounting options depends on the relevant enclosure dimensions |
| To fit                        | Height: = 42 U   |
| Packs of                      | 2 pc(s).   |
| Net weight                    | 11.4   |
| Gross weight                  | 12.04  |
| PCF per pack (cradle-to-gate) | 45.9 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared   |
| Customs tariff number         | 73269098   |
| EAN                           | 4028177955554  |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |