

# Rittal – The System.

Faster – better – everywhere.



## SV 3562.000 Plate clamp

State: 03/07/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3562.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

## Features

|   |  |
|---|--|
| Model No.                                       | SV 3562.000  |
| Product description                             | For connecting laminated copper bars, no drilling required.  |
| Material  | Sheet steel  |
| Surface finish                                  | Zinc-plated, passivated  |
| Clamping area for laminated copper bars (W x H) | 54 x 10 mm   |
| To fit busbars                                  | 50 x 10  |
| To fit busbars                                  | Busbar E-Cu  |
| Packs of  | 3 pc(s).   |
| Net weight                                      | 1.2 kg   |
| Gross weight                                    | 1.412 kg   |
| PCF per pack (cradle-to-gate)                   | 5.4 kg CO2 eq (Cat B)  |
| Note on PCF category                            | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number                           | 85369010   |
| ETIM 9  | EC000001   |
| ETIM 8  | EC000001   |
| ECLASS 8.0                                      | 27141146   |
| Product description                             | SV Plate clamp, for laminated copper bar, clamping area WH: 54x10 mm, for busbar WH: 50x10 mm                  |

## Approvals

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK

## Tender text

SV plate clamps

for E-Cu busbars with 3 - 10 mm thickness.

For bar width: up to 50 mm

Clamping area for laminated copper bars:

54 x 10 mm

Tightening torque:

6 - 8 Nm

Material:

Sheet steel, zinc-plated, passivated