
## Rittal – The System.

Faster – better – everywhere.






# SV 3582.020 CUPONAL busbars

State: 01/12/2025 (Source: rittal.com/com-en)



## SV 3582.020 - CUPONAL busbars

#### Copper-coated aluminium busbar



### **Features**

Model No.	SV 3582.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Length	2,400 mm
Rated current max.	235 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature  Correction factor diagram to DIN EN 43 671  May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	20 mm x 5 mm
Dimensions	Length: 2,400 mm
Packs of	6 pc(s).
Net weight	4.5
Gross weight	6.42
Copper weight (kg per piece)	0.35

© Rittal 2025 2

## Features

Customs tariff number	74071000
EAN	4028177686557
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

## **Approvals**

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3