

Rittal – The System.

Faster – better – everywhere.



SV 3585.020 CUPONAL busbars

State: 23/05/2024 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3585.020 - CUPONAL busbars

Copper-coated aluminium busbar

Features

Model No.	SV 3585.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Length	2,400 mm
Rated current max.	363 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	Flat copper bar width: 20 mm Flat copper bar thickness: 10 mm
Packs of	3 pc(s).
Weight/pack	19.5 kg
Copper weight (kg per piece)	0.7
Customs tariff number	74071000
EAN	4028177686564
ETIM 7.0	EC001522
ECLASS 8.0	27370303

Approvals

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK