Rittal - The System.

Faster – better – everywhere.





AS 4051.222 WT vibratory bowl feeder

State: 08/12/2025 (Source: rittal.com/com-en)



AS 4051.222 - WT vibratory bowl feeder

WT 29 vibratory bowl feeder for guiding loose wire end ferrules with plastic collars for cross-sections 1.5 and 2.5 mm² into the Wire Terminal WT C fully automated wire processing machine.



Features

Model No.	AS 4051.222
Design	WT 29 vibratory bowl feeder
Product description	WT 29 vibratory bowl feeder for guiding loose wire end ferrules with plastic collars for cross-sections 1.5 and 2.5 mm² into the Wire Terminal WT C fully automated wire processing machine.
Benefits	Process reliability with the infeed of wire end ferrules Simple, fast changeover of consumable materials
Technical specifications	Suitable for wire end ferrule lengths from 8 - 18 mm
Supply includes	WT 29 vibratory bowl feeder
Applications	For loose wire end ferrules with cross-section 1.5 mm² and 2.5 mm²
Note	The vibratory bowl feeders and the separation of single wire end ferrules are designed for the dimensional tolerances of Rittal wire end ferrules to DIN 46228-4:2019-02. If the wire end ferrules used exceed the defined dimension tolerances, it may be necessary to design/test a new bowl feeder and to adapt the wire end ferrule separation.
Standards	AEH DIN 46228
To fit Model No.	4051.205 4051.210
Packs of	1 pc(s).
Net weight	0.4

© Rittal 2025

Features

Gross weight	0.7
Customs tariff number	84799070
EAN	4028177981126

© Rittal 2025 3