


Rittal – The System.

Faster – better – everywhere.



AS 4054.870

Cross member cutter


State: 21/01/2026 (Source: rittal.com/com-en)



FRIEDHELM LOH GROUP

AS 4054.870 - Cross member cutter

For cutting through micro webs or sheet steel cross members on Ri4Power interior installation components (for example, compartment dividers) or for cutting thin sheets of sheet steel, aluminium or copper up to 1.2 mm thick.



Features

Model No.	AS 4054.870
Design	Straight
Product description	For cutting through micro webs or sheet steel cross members on Ri4Power interior installation components (for example, compartment dividers) or for cutting thin sheets of sheet steel, aluminium or copper up to 1.2 mm thick.
Benefits	Cutting of materials without deformation Clean edge cuts, no reworking of the cut section required Easy to use Ergonomically styled handles for fatigue-free, non-slip working
Material	Tool body: Special tool steel, rolled, oil-hardened
Colour	Handle: Anthracite and Rittal Power Pink
Supply includes	Cross member cutter including swarf deflector

Features

To fit Model No.	9683.006
	9683.008
	9683.016
	9683.018
	9683.036
	9683.038
	9680.005
	9680.025
	9680.207
	9680.227
	9683.406
	9683.408
	9683.426
	9683.428
	9683.444
	9683.446
	9683.448
	9683.464
	9683.466
	9683.468
	9683.484
	9683.486
	9683.488
Dimensions	Length: 280 mm
Machinable material	Sheet steel Aluminium Copper Plastic
Maximum machinable material thickness, sheet steel	1.2 mm
Maximum machinable material thickness, aluminium	1.2 mm
Maximum machinable material thickness, plastic	2 mm
Cut width	2.7 mm
Packs of	1 pc(s).
Net weight	0.5

Features

Gross weight	0.54
Customs tariff number	82032000
EAN	4028177955929
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890
