Rittal - The System.

Faster – better – everywhere.





AS 4055.180 Splitter hole punch set, metric

State: 19/11/2025 (Source: rittal.com/com-en)



AS 4055.180 - Splitter hole punch set, metric for stainless steel, round, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.180
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 female dies
	5 male dies
	Plastic case
Machinable material	Stainless steel
Maximum machinable material	2 mm
thickness, stainless steel	2 mm
	2 mm
	2.5 mm
	2.5 mm
Ø punch	16.2 mm
	20.4 mm
	25.4 mm
	32.5 mm
	40.5 mm
For threads	M16
	M20
	M25
	M32
	M40
Note	When operating with wrenches, tension screws with ball bearings
	should be used.

© Rittal 2025

Features

Suitable for hydraulic bolt order	4055.665
number	4055.665
	4055.665
	4055.663
	4055.663
Packs of	1 pc(s).
Net weight	0.849
Gross weight	1.098
Customs tariff number	82073010
EAN	4028177808171
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049047

© Rittal 2025 3