Rittal – The System.

Faster – better – everywhere.



PC 5366.150

PC enclosure system

State: 05/11/2026 (Source: www.rittal.com/com-en)

PC 5366.150 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.





Features

Model No.	PC 5366.150
Design	with glazed door at the top, folding keyboard and component shelf
Product description	Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.
Material	Enclosure, door, rear door, mounting compartment, supports: Sheet steel Handles, decorative trim panels: Plastic Door trim panels: Aluminium Viewing window: Single-pane safety glass
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint
General colour	RAL 7035
Colour	Enclosure, door, decorative trim panels, supports: RAL 7035 Handle: RAL 7015 Monitor panel, door centre part: RAL 7015

© Rittal 2026

Features

Supply includes	Enclosure, door, rear door Gland plates Glazed door, top Folding keyboard Component shelf
Dimensions	Width: 600 mm Height: 1,600 mm Depth: 636 mm
IP protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Type rating to 508A	Type 1 Type 12
Max. keyboard dimensions (WxHxD)	497 x 50 x 250 mm 497 x 60 x 200 mm
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	85.5 kg
Gross weight	88 kg
PCF per pack (cradle-to-gate)	373.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC002502
ECLASS 8.0	27180501
Product description	PC PC enclosure system, WHD: 600x1600x636 mm, Sheet steel, with glazed door at the top, folding keyboard, component shelf

Approvals

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

PC Enclosure with glazed door, folding keyboard and component shelf

Enclosure for stand-alone siting, consisting of solid body, glazed door at the top, keyboard drawer, component shelf, bottom door, rear door and welded base assembly. Enclosure body with profiled mounting angles at the front and rear on sidewalls and roof. System slots on a 25 mm pitch pattern, all around, for individual interior installation and two pairs of mounting angles for space-saving system installation.
Glazed door, top:
With support frame latched from the inside, right hinge vertical decorative trim panels, pane with screen-printed mask
Component shelf for monitor:
Perforated, fixed
Folding keyboard:
Housing with mouse support and cut-out in the rear.
Trim panel hinged at the bottom, with 2 retaining cords, with lock insert no. 3524
max. keyboard dimensions (WxHxD): 497x50x250 mm or 497x60x200 mm
Keyboard support with mousepad extension piece
Nylon loop for keyboard
with unlocking device for glazed door, top
Bottom door:
Vertical bars with locking rod and double-bit insert hinged on right-hand side

Door resp. installation plate folded
Rear door:
With locking rod and double bit insert
hinged on right-hand side
With gland plates, divided
Material:
Enclosure, door, rear door, mounting compartment,
supports: sheet steel
Handles, decorative trim panels: plastic
Door trim panels: Aluminium
Viewing window: single-pane safety glass
Gland plate : sheet steel, galvanized
Surface finish:
Enclosure and door: dipcoat primed, powder coated outsidee,
textured paint
Colour:
Enclosure, door, decorative trim panels, supports: RAL 7035
Handles: RAL 7015
Monitor panel, door center part: RAL 7015
Protection class:
IP to IEC 60 529: IP55
NEMA: NEMA 12
Dimensions WHD: 600 x 1600 x 636 mm
Model No: 5366150
Manufacturer: Rittal GmbH & Co.KG

© Rittal 2026