Rittal – The System.

Faster – better – everywhere.



PC 5386.050

PC enclosure system

State: 06/11/2026 (Source: www.rittal.com/com-en)

PC 5386.050 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.





Features

Model No.	PC 5386.050
Design	with glazed door at the top, keyboard drawer and component shelf
Product description	Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.
Material	Enclosure, door, rear door, mounting compartment, supports: Sheet steel Handles, decorative trim panels: Plastic Door trim panels: Aluminium Viewing window: Single-pane safety glass
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint
General colour	RAL 7035
Colour	Enclosure, door, decorative trim panels, supports: RAL 7035 Handle: RAL 7015 Monitor panel, door centre part: RAL 7015

© Rittal 2026

Features

Supply includes	Enclosure, door, rear door Gland plates Glazed door, top Keyboard drawer Component shelf
Dimensions	Width: 800 mm Height: 1,600 mm Depth: 636 mm
IP protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Type rating to 508A	Type 1 Type 12
Max. keyboard dimensions (WxHxD)	480 x 70 x 260 mm
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	114 kg
Gross weight	115.8 kg
PCF per pack (cradle-to-gate)	448.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC002502
ECLASS 8.0	27180501
Product description	PC PC enclosure system, WHD: 800x1600x600 mm, Sheet steel, with glazed door at the top, keyboard drawer, component shelf

Approvals

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

PC Enclosure with glazed door, keyboard drawer and component shelf

Enclosure for stand-alone siting, consisting of solid body, glazed door top, keyboard drawer,
component shelf, bottom door, rear door and welded base assembly. Enclosure body with profiled
Mounting angles at the fronnt and rear on sidewalls and roof. System slots on a 25 mm pitch pattern, all round for individual interior installation and two pairs of mounting angles for space-saving system installation.
Glazed door, top:
With support fram latched from the inside, right hinged vertical decorative trim panels, pane with screen-printed mask
Component shelf for monitor:
Perforated, fixed
Drawer for keyboard:
Enclosure with keyboard extension piece pull-out mousepad front trim panel with handle strip, folded as handrest, with lock insert no.3524 E
with unlocking device for glazed door, top
max. keyboard dimensions (WxHxD): 480x70x260 mm
Bottom door:
Vertical bars with locking rod and double-bit insert
hinged on right-hand side
door resp. installation plate folded
Rear door:
With locking rod and double-bit insert

hinged on right-hand side
Gland plates, divided
Material:
Enclosure, door, rear door, mounting compartment,
supports: Sheet steel
Handles, decorative trim panels: Plastic
Door trim panels: Aluminium
Viewing window: Single-pane safety glass
Gland plate : sheet steel, galvanized
Surface finish:
Enclosure and door: Dipcoat primed,
powder-coated on the outside, textured paint
Colour:
Enclosure, door, decorative trim panels, supports: RAL 7035
Handle: RAL 7015
Monitor panel, door centre part: RAL 7015
Protection class:
IP to IEC 60 529: IP55
NEMA: NEMA 12
Dimensions WHD: 800 x 1600 x 836 mm
Model No.: 5386050
Manufacturer: Rittal GmbH & Co.KG

© Rittal 2026