

Rittal – The System.

Faster – better – everywhere.



AS 4055.480 Hole punch set, metric

State: 02/07/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.480 - Hole punch set, metric for sheet steel

For punching round cut-outs

Features

Model No.	AS 4055.480
Design	With 3 cutting points
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 female dies 5 male dies Plastic case
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm 2 mm 2 mm 2 mm 3 mm
Ø punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm
For threads	M16 M20 M25 M32 M40
Note	When operating with wrenches, tension screws with ball bearings should be used.

Features

Suitable for hydraulic bolt order number	4055.661 4055.661 4055.661 4055.661 4055.663
Packs of	1 pc(s).
Net weight	0.95 kg
Gross weight	0.98 kg
Customs tariff number	82073010
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049047
Product description	Sheet metal punches set, metric Ø 16,2/20,4/25,4/32,5/40,5
