Rittal – The System.

Faster – better – everywhere.



DK 5501.705

Component shelf, static installation

State: 06/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 5501.705 - Component shelf, static installation for VX IT, TS IT, TE, TX CableNet

For static installation between two 482.6 mm (19") mounting levels.





Features

Model No.	DK 5501.705
Benefits	Tool-free, time-saving one-man assembly
Applications	Depth-variable to adapt to individual distances between levels
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	Assembly parts
Installation options	482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear
Load capacity	100 kg
Dimensions	Width: 484 mm
To fit	Enclosure type: VX IT TS IT TE
Distance between levels	600 - 900 mm
Units	1 U
Packs of	1 pc(s).

© Rittal 2026

Features

Net weight	7.6 kg
Gross weight	8.49 kg
PCF per pack (cradle-to-gate)	32.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Component shelf, WxH: 484 mm x 1 U, 100 kg, distance between levels: 600-900 mm, depth-variable, RAL 9005

Tender text

482.6 mm (19") - component shelf, static installation
Depth-variable perforated component shelf, pull-out,
for L-shaped mounting angles and similar mounting
angle shapes. For static installation between two
482.6 mm (19") mounting levels.
Depth-variable to adapt to individual
distances between levels from 600 to 900 mm.
Tool-free, time-saving one-man assembly from
the enclosure front.
Locate, pull-out, snap into position.
Perforated component shelf surface to support
climate control inside the enclosure.
Load capacity 100 kg. Component shelf height 1 U.

Material: Sheet steel
Surface finish: Spray-finished
Colour: RAL 9005
Model No DK: 5501.705
Manufacturer: Rittal