

**Rittal – The System.**

Faster – better – everywhere.



**DK 5501.705**

**Component shelf, static installation**

State: 13/05/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.705 - Component shelf, static installation for VX IT, TS IT, TE, TX CableNet

For static installation between two 482.6 mm (19") mounting levels.



## Features

|                         |   |
|-------------------------|---|
| Model No.               | DK 5501.705   |
| Benefits                | Tool-free, time-saving one-man assembly   |
| Applications            | Depth-variable to adapt to individual distances between levels                                    |
| Material                | Sheet steel   |
| Surface finish          | Spray-finished  |
| Colour                  | RAL 9005  |
| Supply includes         | Assembly parts  |
| Installation options    | 482.6 mm (19") L mounting angles, front and rear<br>482.6 mm (19") mounting frames front and rear |
| Load capacity           | 100 kg  |
| Dimensions              | Width: 484 mm   |
| To fit                  | Enclosure type: VX IT<br>TS IT<br>TE  |
| Distance between levels | 600 - 900 mm  |
| Packs of                | 1 pc(s).  |
| Net weight              | 7.6 kg  |

# Features

|                               |  |
|-------------------------------|--|
| Gross weight                  | 8.49 kg  |
| PCF per pack (cradle-to-gate) | 32.4 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 73269098   |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |
| Product description           | DK Component shelf, WxH: 484 mm x 1 U, 100 kg, distance between levels: 600-900 mm, depth-variable, RAL 9005   |

## Tender text

482.6 mm (19") - component shelf, static installation  
Depth-variable perforated component shelf, pull-out, for L-shaped mounting angles and similar mounting angle shapes. For static installation between two 482.6 mm (19") mounting levels.

Depth-variable to adapt to individual distances between levels from 600 to 900 mm.

Tool-free, time-saving one-man assembly from the enclosure front.

Locate, pull-out, snap into position.

Perforated component shelf surface to support climate control inside the enclosure.

Load capacity 100 kg. Component shelf height 1 U.

Material: Sheet steel

Surface finish: Spray-finished

Colour: RAL 9005

Model No DK: 5501.705

Manufacturer: Rittal