

Rittal – The System.

Faster – better – everywhere.



IW 6900.740 Industrial Workstations

State: 27/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IW 6900.740 - Industrial Workstations

Lower enclosure section, based on VX SE for Industrial Workstations.



Features

Model No.	IW 6900.740
Design	Worktop, keyboard drawer, designer door, rear door
Material	Enclosure, keyboard drawer, designer door and rear door: Sheet steel Worktop: Chipboard (plastic-laminated on both sides (edging))
Surface finish	Enclosure: Dipcoat-primed, powder-coated on the outside, textured paint
Colour	Decorative trim panels: RAL 7015
Supply includes	Enclosure sealed at the sides Three-piece gland plates Levelling feet Worktop, keyboard drawer, designer door, rear door Worktop, W x H x D 610 x 38 x 645 mm
Dimensions	Width: 600 mm Height: 1,000 mm Depth: 645 mm
IP protection category to IEC 60529	IP 54

Features

Dimensions with worktop	Width: 610 mm Height: 1,043 mm Depth: 645 mm
Packs of	1 pc(s).
Net weight	71 kg
Gross weight	74 kg
PCF per pack (cradle-to-gate)	281.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC002502
ETIM 8	EC002502
ECLASS 8.0	27180501
Product description	IW Industrial Workstation, enclosure WHD: 600x900x600 mm, with worktop, keyboard drawer, designer door at the front, rear door

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity