


Rittal – The System.

Faster – better – everywhere.



DK 7066.000 Telescopic slides

State: 02/06/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7066.000 - Telescopic slides for component shelves, for mounting on the VX enclosure frame and for upgrading existing VX and TS applications

For retrospectively converting fixed component shelves to full withdrawal by exchanging the fastening bolts or mounting rails (heavy-duty version) for the telescopic slides.

Features

Model No.	DK 7066.000
Product description	Fixed component shelves are easily converted to full withdrawal. For this purpose, the existing fastening bolts or mounting rails (heavy-duty version) are exchanged for the telescopic slides.
Material	Sheet steel
Surface finish	Zinc-plated
Suitable for component shelf depth	600 mm
Load capacity	100 kg
Note	For installation and locking on a 25 mm pitch pattern in the enclosure depth.
Packs of	2 pc(s).
Net weight	3.47 kg
Gross weight	3.66 kg
PCF per pack (cradle-to-gate)	14 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Telescopic slides for component shelf, 100 kg, For D: 600 mm

Tender text

Telescopic slides for 600 mm deep component shelves

Version: max. load capacity 100 kg

The telescopic slides are installed between the installation kit and a 600 mm deep component shelf. The telescopic slides have a maximum load capacity of 100 kg and are lockable in two positions.

Material: sheet steel, zinc-plated

For component shelf depth: 600 mm