

Rittal – The System.

Faster – better – everywhere.



CP 6148.000 Twin castors

State: 08/05/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6148.000 - Twin castors

For mobile use, for mounting directly on the enclosure.

Features

Model No.	CP 6148.000
Product description	For mobile use, for mounting directly on the enclosure.
Colour	Black with grey running surface
Supply includes	4 twin castors, 2 x with, 2 x without locks Assembly parts
To fit	Enclosure type: VX Enclosure type: VX IT Enclosure type: TS Enclosure type: TS IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Chiller
Clearance floor	85 mm
Max. load capacity (static) per component	750 N
To fit Model No.	Standfuß 6106.200 Standfuß 6106.300
Dimensions	Thread: M12 x 20
Packs of	1 pc(s).
Net weight	1.115
Gross weight	1.293
Customs tariff number	83024900
EAN	4028177206007
E-Number Sweden	E7239728

Features

ETIM 9	EC002621
ECLASS 8.0	27189262
