


# Rittal – The System.

Faster – better – everywhere.



DK 7827.221

Mounting angles, 482.6 mm (19")

State: 08/02/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

# DK 7827.221 - Mounting angles, 482.6 mm (19") for TS

L-shaped mounting angles, also for accommodating server system installation kits.

## Features

Model No.	DK 7827.221
Design	L-shaped mounting angle
Benefits	<p>Integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level.</p> <p>L-shaped mounting angles accommodate the installation kits of server systems</p> <p>Suitable for 482.6 mm (19") partial installation</p>
Technical specifications	<p>Integral 482.6 mm (19") punchings (EIA standard)</p> <p>Side round and square punchings</p> <p>Clear chromated for conductive connection of the 482.6 mm (19") installed equipment.</p>
Material	Sheet steel, 2 mm
Supply includes	Assembly parts
Units	47 U
Note	<p>Please select slide rails according to the relevant 482.6 mm (19") distance between levels.</p> <p>If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used.</p>
To fit	<p>Enclosure type: TS</p> <p>Height: 2,200 mm</p>
Packs of	2 pc(s).
Net weight	4.958
Gross weight	5.218
Customs tariff number	73269098
EAN	4028177234987
ETIM 9	EC002620

# Features

---

ECLASS 8.0

27189261

## Tender text

DK-TS mounting angles, L-shaped, 47 U

Technical specifications: 2 mm sheet steel, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and square holes. Zinc-plated, passivated for conductive connection to the installed 482.6 mm (19") equipment.

Material: Sheet steel, zinc-plated, passivated