

Rittal – The System.

Faster – better – everywhere.



DK 7240.305

Socket strip

State: 02/08/2025 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7240.305 - Socket strip with ammeter

For measuring the power consumption of the connected consumers, pin patterns: "earthing pin", various mounting options

Features

Model No.	DK 7240.305
Product description	The socket strip with ammeter measures the active power of the connected equipment. The 482.6 mm (19") long socket strip may optionally be mounted on the 482.6 mm (19") mounting frame, on the enclosure frame or in the rear section of wall-mounted distributors. The installation bracket may be mounted in four different positions for variable mounting. Without additional mounting accessories, the socket strip may be inserted into all sections with a 25 mm pitch pattern.
Material	Aluminium section, natural anodised Socket inserts: Polycarbonate
Supply includes	Socket strip Two installation brackets Assembly parts With 3 m connection cable (wire end ferrules)
Design	With ammeter
Sockets	8 x IEC 320 socket C13
Dimensions	Height: 45 mm Depth: 50 mm Length: 482.6 mm
Length of connection cable	3 m
Mounting dimensions	464.1 mm
Rated operating voltage	250 V AC, 50 Hz
Rated voltage	230 V AC, 50 Hz
Rated current (max.)	10 A

Features

Installation options	Components with a 25 mm pitch pattern Enclosure frame IT wall-mounted distributor, at the rear, horizontal (adequate width provided) 482.6 mm (19") level
Packs of	1 pc(s).
Net weight	1.1
Gross weight	1.14
Customs tariff number	85366990
EAN	4028177558151
ECLASS 8.0	27142604

Tender text

Socket strip, 8 way multi-socket C13 max 10A/socket

2 angle brackets are needed to fix the socket strip in the network enclosure.

The socket strip is designed with 8 IEC320 appliance sockets in accordance with standard specifications sheet F. The ammeter shows the flowing current with a two digit 7 segment display. It is an aluminium section, natural anodised enclosure. The socket cups are made from polycarbonate.

Technical specifications:

- Dimensions 482.6 length, 44.45 mm width, 44.45 mm height
- Rated current: 16 A
- Rated voltage: 230V
- Protection category: IP20
- Conformity: CE following directive 72/73/EWG, ROHS following directive 2002/95/EC
- Safety: DIN EN 60950-1
- Connection cables: 1.5 m, grey, without connector, H05VV-F3G1.5