
### Rittal - The System.

Faster – better – everywhere.





### DK 7464.035

# Component shelf for frame attachment

State: 02/11/2025 (Source: rittal.com/com-en)



## DK 7464.035 - Component shelf for frame attachment for enclosure widths 600 mm, 800 mm

For installation in enclosures without 482.6 mm (19") accommodation.

### **Features**

| Product description | Slotted  For frame attachment, for installation in enclosures without 482.6   |
|---------------------|---|
| ·                   | For frame attachment, for installation in enclosures without 482.6  |
|                     | mm (19") accommodation.   |
|                     | Mounting bolts or mounting rails may be installed on a 25 mm pitch pattern in the enclosure depth.  Mounting hole for handles provided.   |
| • •                 | For installation in enclosures without 482.6 mm (19") accommodation   |
| Material            | Sheet steel   |
| Surface finish      | Spray-finished  |
| Colour              | RAL 7035  |
|                     | Component shelf, slotted<br>2 mounting rails  |
|                     | Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange Depth variable: Component shelf, 50 kg with telescopic slides on punched sections without mounting flange |
| Load capacity       | 100 kg area load  |
| •                   | Additionally, two punched sections with mounting flanges are required for the inner mounting level  |
| Note                | Max. depth of component shelves = Enclosure depth - 100 mm.   |

© Rittal 2025 2

### **Features**

| Dimensions                    | Width: 471 mm  |
|-------------------------------|--|
|                               | Height: 45 mm  |
|                               | Depth: 400 mm  |
| To fit                        | Enclosure type: VX   |
|                               | VX IT  |
|                               | TS IT  |
|                               | Width: 600 mm  |
| Packs of                      | 1 pc(s).   |
| Net weight                    | 5.348  |
| Gross weight                  | 5.629  |
| PCF per pack (cradle-to-gate) | 21.4 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 94039910   |
| EAN                           | 4028177165977  |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |

© Rittal 2025 3

#### Tender text

Component shelves for 600 mm wide network enclosures

Component shelves for 600 mm wide network enclosures Version: Max. load capacity 100 kg
Component shelves, W x D = 471 x 400 mm, 2 mm thick sheet steel version; for installing in 600 mm wide network enclosures.

The component shelf is slotted to prevent the accumulation of heat. The component shelves can hold a maximum load of 100 kg.

The height of the fitted component shelves can be adjusted using the 25 mm pitch pattern in network enclosures with a DIN pitch pattern but is infinitely adjustable in network enclosures with aluminium frames.

Material: Sheet steel Spray finish: RAL 7035

Dimensions: W x D: 471 x 400 mm

© Rittal 2025 4