


# Rittal – The System.

Faster – better – everywhere.



## DK 7979.813 PDU UK basic

State: 15/04/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7979.813 - PDU UK basic

The power distributor is specifically designed for data centres and free-standing racks with UK (BS 1363) connectors.



## Features

|                          |  |
|--------------------------|--|
| Model No.                | DK 7979.813  |
| Product description      | High-end power distribution in a compact design for IT network and server racks. Depending on the design, they come with an extensive range of management functions for energy measurement and monitoring.   |
| Benefits                 | Tool-free divider kit for VX IT<br>Power-saving design, minimal intrinsic power consumption  |
| Technical specifications | Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white)  |
| Material                 | Aluminium section, black anodised<br>Slots: Plastic  |
| Supply includes          | Assembly parts   |
| Options                  | Type 3 overvoltage protection with interchangeable arresters while operational, with status monitoring, suitable for integration into PDU enclosure<br>Type 3 overvoltage protection with interchangeable arresters while operational, with status monitoring, suitable for integration into PDU enclosure |
| Dimensions               | Width: 44 mm<br>Depth: 70 mm<br>Length: 1,095 mm   |
| No. of sockets and type  | 16 x BS 1363   |

# Features

|                                   |   |
|-----------------------------------|---|
| Sockets                           | 16 x BS 1363  |
| Rated current (max.)              | 13 A  |
| Power consumption                 | 3 kW  |
| Infeeds                           | Qty.: 1<br>Phases per infeed: 1~  |
| Length of connection cable        | 3 m   |
| Type of electrical connection     | UK  |
| Directives                        | EMC Directive 2014/30/EU<br>Low Voltage Directive 2014/35/EU  |
| Standards                         | EN 62368-1<br>EN 61000-3<br>EN 61000-4<br>EN 61000-6<br>EN 62053-21   |
| Operating temperature range       | 5 °C...50 °C  |
| Ambient humidity (non-condensing) | 10...95 %   |
| Storage temperature range         | -25 °C...70 °C  |
| To fit                            | Enclosure type: VX IT enclosure frame: ≥ 1,200 mm<br>Enclosure type: VX IT 19" mounting angles: ≥ 1,800 mm<br>Enclosure type: TX CableNet: ≥ 1,200 mm |
| Packs of                          | 1 pc(s).  |
| Customs tariff number             | 85366990  |
| ETIM 9                            | EC000330  |
| ETIM 8                            | EC002762  |
| ECLASS 8.0                        | 27142604  |
| Product description               | DK PDU UK basic, compact basic power distribution, WLD:<br>44x1095x70 mm, 16x BS 1363, 230 V, 1~, 13 A  |

# Approvals

---

Explanations

Declaration of conformity

## Tender text

Rittal PDU Basic UK Model No.: DK 7979.813

Compact power distributor for deployment in IT server and network enclosures. Vertical installation in the Zero-U space using the supplied universal brackets for common IT racks. Suitable for tool-free quick assembly in the Rittal VX IT and TS IT racks using the special supplied plug-%-play fastener. Robust aluminium housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19 as well as CEE 7/3 (earthing-pin) and BS 1363 (UK), depending on the type (see below for details). The IEC C13 / C19 output slots can be protected with a lock against unintentional removal of the connectors. Unused slots can be closed with slot covers available as accessories. This precludes an unintentional overloading of individual phases and circuits. The fuse circuits and phases are colour-coded for multiphase PDU variants. A fixed-mounted connection cable with IEC C20 or CEE connector appropriate for the variant makes the PDU available for immediate deployment. Optionally, an overvoltage protection module (type3) can be placed on the PDU at the infeed; the overvoltage protection module is equipped with arrestors that can be replaced during operation. For intelligent PDUs, the status is monitored via the network interface, the PDU basic has a floating alarm contact for monitoring the overvoltage protection. As option, intelligent PDU variants can be supplied with an AC/DC sensitive residual current measurement (RCM type B) with up to 6 measurement points. This changes the PDU length and the number of installed slots for each standard length.

## Technical specifications basic

Input voltage range (L/N/PE): 230 VAC, 50-60Hz

input current: 13A

No. of phases: 1

Marking of phases (3-phase PDU only L1, L2, L3):

Rittal Power Pink, black, white

Number of slots type BS1363 (total): 16

No. of circuit breakers: -

Hydraulic-magnetic protective circuit-breaker: 16 A

Connector PDU input: BS1363

Length of connection cable: 3m

Connection cable type: H05-VV

No. of wires: 3

Cable cross-section: 1,5 mm<sup>2</sup>

PDU housing width: 44mm

PDU housing depth: 70mm

PDU housing height: 1095mm

PDU material: Aluminium, anodised, in RAL 9005 (black)<(,>,<)>

other colours available on request

PDU mounting adaptor (VX IT / TS IT)-Mounting options:

Frame+Zero-Uospace+cable route, fuse monitoring

Conformity: CE

Standards:

Safety: EN 62368

EMC:

EN 55022 / B

EN 61000-4-2

EN 61000-4-3

EN 61000-6-2

EN 61000-6-3

Low Voltage Directive: 2014/35/EU

EMC Directive: 2014/30/EU

MTBF (at 40°C) 100.000 hours

Protection category: IP20 (EN 60529)

Protection class: Class 1

Pollution degree: 2

Overvoltage category: II

Environmental properties: 2011/65/EU (RoHS 2), WEEE

Storage temperature: -20 °C to +70 °C

Ambient temperature: +5°C to +50°C

Ambient humidity 10 - 95% rel. humidity, non-condensing

Operating altitude (max. above mean sea level): 3000 m

Connector lock for C14 and C20 connectors:

1x (further connector locks optional - DK 7979.020)

Covers C13 (optional accessory): DK 7955.010

Covers C19 (optional accessory): DK 7955.015

Type: Rittal PDU basic, Model No.: DK 7979.813