
Rittal – The System.

Faster – better – everywhere.



DK 7543.000

Earth rail, vertical

State: 07/11/2026 (Source: www.rittal.com/com-en)

DK 7543.000 - Earth rail, vertical for VX, VX IT

The supplied earth conductors facilitate star earthing of the cable clamp straps in the patch panels, the earth terminals are fully adjustable, current carrying capacity of rails approx. 200 A.

Features

Model No.	DK 7543.000
Product description	Easily fitted to the 25 mm DIN pitch pattern of distributors or to the 482.6 mm (19") mounting angles. The supplied earth conductors facilitate star earthing of the cable clamp straps in the patch panels. The earth terminals are fully adjustable. Current carrying capacity of rail approx. 200 A.
Supply includes	Earth rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm null 15 earthing leads 6 mm², L = 500 mm Assembly parts
Dimensions	Length: 945 mm
To fit	Enclosure type: VX VX IT TS Height: 1,200 mm
Packs of	1 pc(s).
Net weight	1.581 kg
Gross weight	1.8 kg
Customs tariff number	74198090
ETIM 9	EC000329
ECLASS 8.0	27400605
Product description	DK earth rail, vertical, L: 945 mm, for height 1200 mm, earthing leads: 15x 6 mm², L: 500 mm, conductor connection clamps: 16x 2.5-16 mm²

Tender text

Earth rail for 1200 mm high network enclosures
For the vertical installation in 1200 mm high network enclosures.
Earth rail made from E-Cu 57 (15 x 5 mm) to DIN 1759, DIN 40 500 is fitted to the 482.6 mm (19 inch) mounting angles or to the 25 mm DIN 43 660 pitch pattern of distributors.
The supplied earth conductors facilitate star earthing of the cable clamp straps in the patch panels. The earth terminals are fully adjustable.
Current carrying capacity of rail approx. 200 A.

For network enclosure H: 1200 mm
Length of earth rail: 945 mm

© Rittal 2026