

# Rittal – The System.

Faster – better – everywhere.



## DK 7979.504 PDU metered plus

State: 26/05/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7979.504 - PDU metered plus

High-end IT rack power distribution: Smart PDU with energy measurement per slot, i.e. output requirement for each individual consumer.



## Features

|                     |   |
|---------------------|---|
| Model No.           | DK 7979.504   |
| Design              | 482.6 mm (19") version  |
| Product description | High-end power distribution in a compact design for IT network and server racks. With power measurement per individual outgoing slot.   |
| Benefits            | <p>For vertical mounting, it may be attached in the zero-U space of the Rittal VX IT or TS IT rack with no need for tools</p> <p>Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white)</p> <p>Tool-free divider kit for VX IT</p> <p>PDU self-supplied, no external power supply required</p> <p>Measurement accuracy <math>\pm 1\%</math> (kWh) to EN 62 053-21</p> <p>Integral real-time clock with battery buffering (max. 10 years, battery replaceable)</p> <p>Integral electromagnetic buzzer for acoustic alarms</p> <p>Adjustable limit values (warning/alarm) for current, voltage, output, individual settings for each output slot</p> <p>Power-saving design, minimal intrinsic power consumption</p> |

# Features

|                                    |  |
|------------------------------------|--|
| Technical specifications           | Display/controller unit in the PDU enclosure rotatable through 180° and replaceable<br>Integral, fully-redundant power pack, power supply from all phases<br>Error-tolerant PDU power supply redundant across all phases<br>Voltage V, current A, frequency Hz<br>Active power, active energy, apparent power, apparent energy<br>Power factor (cosPhi) and phase angle<br>Zero conductor current measurement/load imbalance detection<br>Fuse monitoring for PDUs with integral fuse<br>Bright TFT display, 128 x 128 pixels (RGB) with back-lighting and energy-saving mode to display output data and basic PDU configuration<br>Position sensors for display rotation and correct PDU representation on the website<br>Multi-colour LEDs (green/amber/red) to indicate switching states and limits per individual output slot<br>Power LED to indicate voltage |
| Material                           | Aluminium section, black anodised<br>Slots: Plastic  |
| Supply includes                    | Assembly parts   |
| Options                            | CMC III CAN bus sensors may be connected for ambient monitoring, max. 16 sensors   |
| Measurement functions, description | Measurement per phase or infeed<br>Plus measurement per output slot<br>Powerful CPU (ARM Cortex A8)<br>Digital input (floating contact)<br>Additional alarm output/relay output (changeover contact)   |
| Dimensions                         | Height: 44 mm<br>Depth: 144 mm<br>Length: 450 mm   |
| No. of sockets and type            | 4 x C13 / 2 x C19  |
| Sockets                            | 4 x C 13<br>2 x C 19   |
| Rated operating voltage            | 230 V (AC)   |
| Rated current (max.)               | 32 A   |
| Power consumption                  | 7.4 kW   |

# Features

|  |  |
|--|--|
| Infeeds                                | Qty.: 1<br>Phases per infeed: 1~   |
| Length of connection cable             | 3 m  |
| Type of electrical connection          | CEE  |
| Interfaces                             | USB 2.0 port (USB-A) for mass configuration, firmware updates & data logging<br>CAN bus interface (RJ 45) for a maximum of 16 ambient sensors<br>Serial interface RS232 (RJ12) for LTE unit, scripting, CLI<br>Use of own certificates/TLS 1.2<br>E-mail forwarding in case of alarm (SMTP)<br>User administration including rights management<br>LDAP(S)/Radius/Active Directory connection<br>Syslog server connection (max. 2 servers)<br>Fully redundant Ethernet interface 10/100/1000 Mbit/s |
| Number RJ45 ports for sensor units max | 2  |
| Directives                             | EMC Directive 2014/30/EU<br>Low Voltage Directive 2014/35/EU   |
| Standards                              | EN 62368-1<br>EN 61000-3<br>EN 61000-4<br>EN 61000-6<br>EN 62053-21  |
| Protocols                              | Web server (HTTP, HTTPS, SSL) SSH, Telnet, NTP<br>TCP/IP v4 & v6, DHCP, DNS<br>SNMP v1, v2c & v3, Modbus/TCP, OPC-UA<br>MIB for linking into 3rd party DCIM software<br>FTP/SFTP (update/file transfer)  |
| Operating temperature range            | 5 °C...50 °C   |
| Ambient humidity (non-condensing)      | 10...95 %  |
| Storage temperature range              | -20 °C...70 °C   |
| To fit                                 | Enclosure type: VX IT enclosure frame: ≥ 800 mm<br>Enclosure type: VX IT 19" mounting angles: ≥ 800 mm   |
| Packs of                               | 1 pc(s).   |

# Features

---

|                       |  |
|-----------------------|--|
| Customs tariff number | 85366990   |
| ETIM 9                | EC002762   |
| ETIM 8                | EC002762   |
| ECLASS 8.0            | 27142604   |
| Product description   | DK PDU metered+, compact basic power distribution incl. energy measurement per output slot, with network interface and display, WLD: 450x44x144 mm, IEC 60 320: 4x C13, 2x C19 |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | Cyber Security Certificate<br>TÜV-tested safety |
| Explanations | Declaration of conformity                       |

# Tender text

Compact power distributor for deployment in IT server and network enclosures. Robust aluminium housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19 as well as CEE 7/3 (earthing-pin) and BS 1363 (UK), depending on the type (see below for details). The IEC C13 / C19 output slots can be protected with a lock against unintentional removal of the connectors. Unused slots can be closed with slot covers available as accessories. This precludes an unintentional overloading of individual phases and circuits. The fuse circuits and phases are colour-coded for multiphase PDU variants. A connection cable with IEC C20 or CEE connector appropriate for the variant makes the PDU available for immediate deployment.

The PDU metered plus has extensive measurement functions for the current and power monitoring of each output slot. The integral TFT colour display enables the basic configuration setting and quick access to the electrical consumption data. Two Gigabit network interfaces and the integrated Web server allow remote access and data transmission using various protocols. The consumption parameter can be SNMP, OPC-UA, Modbus/TCP. For monitoring the ambient parameters, up to 16 sensors (for example temperature / humidity / smoke / leakage / access) as well as VX IT and TS IT handle systems from the CMC accessories program can be connected to the CAN sensor interface.

Technical specifications metered plus

Input voltage range (L/N/PE): 230 VAC, 50-60Hz

input current: 32A

No. of phases: 1

Marking of phases (3-phase PDU only L1, L2, L3):

Rittal Power Pink, black, white

Number of slots type IEC 60320/C13 (total): 4

Number of slots type IEC 60320/C13

(per phase/fuse): 4 / 2

Number of slots type IEC 60320/C19 (total): 2

Number of slots type IEC 60320/C19  
(per phase/fuse): 2 / 1  
Number of slots type CEE 7/3 (total): -  
Number of slots type CEE 7/3  
(per phase/fuse): -  
No. of circuit breakers: 2  
Hydraulic-magnetic protective circuit-breaker: 16 A  
Connector PDU input:  
EN 60309 / CEE (L+N+PE,6h)  
Length of connection cable: 3m  
Connection cable type: H05-VV  
No. of wires: 3  
Cable cross-section: 4 mm<sup>2</sup>  
PDU housing width: 450mm  
PDU housing depth: 144mm  
PDU housing height: 44mm (1HU)  
PDU Material: Aluminium,eloxiert in RAL 9005 (schwarz)<(,<)>  
other colours available on request  
PDU mounting adaptor (VX IT / TS IT) –Mounting options:  
Frame + Zero-U space + cable route  
Measurement functions: Measurement per output slot  
Values recorded (per output slot): Voltage (V)  
current (A), frequency (HZ), active power (kW),+  
active energy (kWh), apparent energy (kVAh)<(,<)>  
apparent power (kVA), reactive power (var),power factor  
THD (voltage and current) for 3 phases<(,<)>  
Crest factor for single-phase, Ne  
neutral conductor current measurement  
fuse monitoring (at 32 A)  
Optional: Residual current monitoring (RCM): RCM Typ B  
max. 6 measurement points per PDU possible<(,<)>  
(input / per phase / per fuse)<(,<)>  
0 mA – 100 mA je RCM  
Voltage measurement range: 90 – 255 V  
Voltage resolution: 0.1 V  
Current measuring range 0 - 16A/32A  
Current resolution: 0.01 A  
Measurement accuracy (measurement error, typ.): 1 %  
Freely settable limit values per slot  
Controllerboard: can be rotated  
and replaced during operation  
Display: TFT, RGB 128x128 pixels

Network interface: 2x RJ45, je 10/100/1000 MBit/s  
Supported protocols: IPv4 / IPv6(>,<)>  
integral web server, HTTP, HTTPS(>,<)>  
SSL, SSH, NTP, Telnet, TCP/IP v4 und v6, DHCP, DNS(>,<)>  
NTP, Syslog, SNMP v1, v2c und v3, Traps, OPC-UA(>,<)>  
Modbus/TCP, FTP/SFTP (update/file transfer)<(>,<)>  
E-mail forwarding (SMTP)  
User administration including rights management: Yes  
LDAP(S)/Radius connection: Yes  
USB port for firmware update  
and data logging functions: Yes  
Initial commissioning / mass configuration:  
yes, with predefined CSV file  
CAN bus interface: RJ45, for connecting 16 sensors  
CAN sensor types: Temperature, temperature/humidity<(>,<)>  
infrared access sensor, leakage, airflow  
EFD, NH measurement module, smoke alarm, vandalism  
differential pressure, VX IT / TS IT handle system  
Plug & play drivers - Rittal RiZone DCIM software: Yes  
Digital input: 1  
Alarm relay: 48 V DC/2 A  
Acoustic signal encoder  
Serial interface:  
RS232 (e.g. for LTE unit 7030.571)  
Conformity: CE  
Standards:  
Safety: EN 62368  
EMC: EN 55022 / B  
EN 61000-4-2  
EN 61000-4-3  
EN 61000-6-2  
EN 61000-6-3  
Low Voltage Directive: 2014/35/EU  
EMC Directive: 2014/30/EU  
MTBF (bei 40°C): 100.000 hours  
Protection category: IP20 (EN 60529)  
Protection class: 1  
Pollution degree: 2  
Overvoltage category: II  
Environmental properties: 2011/65/EU (RoHS 2), WEEE  
Storage temperature: -20°C to +70°C  
Ambient temperature: +5°C to +50°C

Ambient humidity: 10-95% rel. humidity, non-condensing

Operating altitude (max. above mean sea level): 3000 m

Connector lock for C14 and C20 connectors:

1x (further connector locks optional - DK 7979.020)

Covers C13 (optional accessory): DK 7955.010

Covers C19 (optional accessory): DK 7955.015

Type: Rittal PDU metered+ Model No.: DK 7979.504