## Rittal – The System.

Faster - better - everywhere.





# SK 7980.000 Fan expansion kit

State: 18/11/2025 (Source: rittal.com/com-en)



## SK 7980.000 - Fan expansion kit

For retrofitting various fan units or to supplement the fan mounting plate

#### **Features**

Model No.	SK 7980.000
Product description	For use as a stand-alone fan, and for upgrading various fan units of to supplement the fan mounting plate.
Supply includes	Fan
	Connection cable (0.61 m)
	Assembly parts
Air throughput, unimpeded airflow	At 50 Hz: 160 m³/h
(with chopped-fibre filter)	At 60 Hz: 180 m³/h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 15 W
	At 60 Hz: 14 W
Dimensions	Width: 119 mm
	Height: 119 mm
	Depth: 38 mm
Operating temperature range	-10 °C55 °C
Noise level	At 50 Hz: 37 dB(A)
	At 60 Hz: 37 dB(A)
Packs of	1 pc(s).
Net weight	0.6
Gross weight	0.671
Customs tariff number	84145915
EAN	4028177137752
ETIM 9	EC000320
ECLASS 8.0	27180716

© Rittal 2025

### Tender text

Fan expansion kit for fan mounting plate

Rated operating voltage: 230V; Power consumption: 19/18

W at 50/60 Hz;

Air throughput (unimpeded air flow): 160 - 180 m³/h at

50/60 Hz;

Temperature range: -10°C to +55°C

Dimensions (W x H x D): 119 mm x 119 mm x 38 mm

© Rittal 2025 3