



Rittal – The System.

Faster – better – everywhere.



VX 8618.821 EMC gland plate

State: 16/08/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8618.821 - EMC gland plate for VX

For shielded cables with a maximum diameter of 20 mm. Combined EMC contacting and cable fastening provide low-resistance contact between the cable shield and gland plate. For all 400, 500, 600 and 800 mm deep enclosures in conjunction with standard gland plates.

Features

Model No.	VX 8618.821
Product description	For shielded cables with a maximum diameter of 20 mm. Combined EMC contacting and cable fastening provide low-resistance contact between the cable shield and gland plate. For all 400, 500, 600 and 800 mm deep enclosures in conjunction with standard gland plates.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	1 gland plate with T-head punching 1 sliding gland plate 2 EMC seals
To fit	Enclosure type: VX Width: = 800 mm
Note	Standard-compliant IP protection category not supported
Packs of	1 pc(s).
Net weight	2.5
Gross weight	2.72
Customs tariff number	94039910
EAN	4028177929890
ETIM 9	EC002620
ECLASS 8.0	27189261