Rittal – The System.

Faster – better – everywhere.



# VX 8620.091

# Base/plinth trim panels, vented

State: 02/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# VX 8620.091 - Base/plinth trim panels, vented for base/plinth system VX

For venting the enclosure via the base/plinth. Specifically in applications such as power distribution where the enclosure gland plates are not used, this can be used to achieve a higher air throughput inside the enclosure. Various solutions to raise the roof and special roof plates with vent openings are also available for enclosure venting. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Thanks to the complete symmetry of the base/plinth system VX, the trim panels may either be fitted at the front, rear or side on the base/plinth corner piece.

## Features

| | |
|---|---|
| Model No. | VX 8620.091 |
| Product description | For venting the enclosure via the base/plinth. Specifically in applications such as power distribution where the enclosure gland plates are not used, this can be used to achieve a higher air throughput inside the enclosure. Various solutions to raise the roof and special roof plates with vent openings are also available for enclosure venting. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Thanks to the complete symmetry of the base/plinth system VX, the trim panels may either be fitted at the front, rear or side on the base/plinth corner piece. |
| Material | Sheet steel |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Dimensions | Height: 100 mm |
| To fit | Enclosure type: VX<br>TX CableNet<br>Width/depth: 800 mm |
| Type rating to UL 50E | Type 1, 12 |
| Weight/pack | 1.95 kg |
| Packs of | 2 pc(s). |

# Features

| | |
|---|---|
| Net weight | 1.8 kg |
| Gross weight | 2.2 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX Base/plinth trim panel, vented, for W/D: 800 mm, sheet steel |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL - FTTA |