


Rittal – The System.

Faster – better – everywhere.



TS 8609.850 Divider panel

State: 11/04/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8609.850 - Divider panel for TS

For shielding individual enclosure cells. Thanks to the symmetry of the frame system, the divider panel can also be used at the rear.



Features

| | |
|----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | TS 8609.850 |
| Product description | For shielding individual enclosure cells. All-round, double fold for stability and to hold the seal. Thanks to the symmetry of the enclosure frame, divider panels may also be fitted at the rear, dimensions permitting. |
| Applications | Notches in the corners and half-way up the sides permit the use of angular baying brackets and baying brackets, even with a divider panel fitted. |
| Material | Sheet steel, 1.5 mm |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| To fit | Enclosure type: TS 8 Height: = 1,800 mm Depth: = 500 mm |
| Installation options | For mounting on the outer mounting level This leaves the inner level free for further population |
| Assembly instruction | The divider panel may also be fitted at the rear. This allows, e.g. frequency converters for heat dissipation to be installed in a divider panel with the cooling units facing outwards and protected/finished off with a cover. |

Features

| | |
|-------------------------------------|-----------------------------------------------|
| IP protection category to IEC 60529 | IP 54 |
| Packs of | 1 pc(s). |
| Net weight | 9.633 kg |
| Gross weight | 10.14 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002525 |
| ECLASS 8.0 | 27182102 |
| Product description | TS Divider panel, for TS, for WD: 1800x500 mm |
