
## Rittal - The System.

Faster – better – everywhere.





# TS 8800.754 Cable duct

State: 19/11/2025 (Source: rittal.com/com-en)



#### TS 8800.754 - Cable duct

With special DIN punchings for direct mounting on the enclosure section or on surfaces such as mounting plates. Nominal break points on the bars and on the cable duct base.





#### **Features**

Model No.	TS 8800.754
Design	for mounting plates For mounting on VX system punchings
Product description	With special DIN punchings for direct mounting on the enclosure section or on surfaces such as mounting plates. Nominal break points on the bars and on the cable duct base.
Material	Hard PVC Flame-resistant, self-extinguishing Temperature resistant to +60 °C
Colour	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm
Slot width	4.5 mm
Installation options	With special DIN punchings for direct mounting on the enclosure section or on surfaces such as mounting plates If the mounting plate is installed flush with the enclosure frame at the rear (installation position ±0 mm), the horizontally mounted cable ducts are aligned with the cable ducts mounted on the enclosure section. Cable duct 100 mm for mounting on the vertical enclosure frame with bayed enclosures.

© Rittal 2025

### Features

Note	Can be shortened for other dimensions.
Dimensions	Width: 100 mm
	Depth: 80 mm
	Length: 2,000 mm
Packs of	12 pc(s).
Net weight	21.96
Gross weight	23.58
Customs tariff number	39259020
EAN	4028177445482
ETIM 9	EC000012
ECLASS 8.0	27400703

## Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3