


# Rittal – The System.

Faster – better – everywhere.



## VX 8618.823 EMC gland plate

State: 24/08/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8618.823 - EMC gland plate for VX

For shielded cables with a maximum diameter of 20 mm. Combined EMC contacting and cable fastening provide low-resistance contact between the cable shield and gland plate. For all 400, 500, 600 and 800 mm deep enclosures in conjunction with standard gland plates.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | VX 8618.823  |
| Product description   | For shielded cables with a maximum diameter of 20 mm. Combined EMC contacting and cable fastening provide low-resistance contact between the cable shield and gland plate. For all 400, 500, 600 and 800 mm deep enclosures in conjunction with standard gland plates. |
| Material              | Sheet steel  |
| Surface finish        | Zinc-plated  |
| Supply includes       | 1 gland plate with T-head punching<br>1 sliding gland plate<br>2 EMC seals   |
| Note on Model No.     | For one enclosure half only  |
| To fit                | Enclosure type: VX<br>Width: = 1,200 mm  |
| Note                  | Standard-compliant IP protection category not supported  |
| Packs of              | 1 pc(s).   |
| Net weight            | 2  |
| Gross weight          | 2.14   |
| Customs tariff number | 94039910   |
| EAN                   | 4028177929876  |
| ETIM 9                | EC002620   |
| ECLASS 8.0            | 27189261   |