


**Rittal – The System.**

Faster – better – everywhere.



**SV 9340.950**

**Bus-mounting fuse base D-Switch**

State: 05/04/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.950 - Bus-mounting fuse base D-Switch

With integral visual fuse monitoring via flashing indicator and operating status display.

## Features

|   |   |
|---|---|
| Model No.                                     | SV 9340.950   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Colour  | Chassis: RAL 7035<br>Fuse holder: RAL 7001  |
| Supply includes                               | Retaining springs for D 01 and 10 x 38 mm fuses   |
| Note  | Wire end ferrules should be used with fine wire conductors  |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Type of electrical connection                 | Box terminal  |
| Fuse inserts                                  | D 01 (with reducer)<br>D 02 (with Neozed adaptor sleeve)<br>10 x 38 (with retaining spring)   |
| Fuse inserts footnote                         | When using D 01 and 10 x 38 mm fuses, reducers must be used.<br>Use of D 01 fuses optionally possible with adaptor sleeve for D 02 base/plinths.  |
| Rated operating current max.                  | 63 A  |
| Rated operating voltage                       | 400 V   |
| Note  | For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3)<br>With integral visual fuse monitoring via flashing indicator and operating status display as well as cable routing for conductors up to 6 mm <sup>2</sup> |
| Test specification                            | IEC/DIN EN 60 947-3   |
| Dimensions                                    | Width: 27 mm<br>Height: 226 mm  |
| Connection of round conductors                | 1.5 - 25 mm <sup>2</sup>  |

# Features

|                                    |   |
|------------------------------------|---|
| To fit busbars                     | Height: 5, 10 mm  |
| Voltage range for indicator lights | 100 - 400 V   |
| Number of poles                    | 3-pole  |
| Round conductor cross-section      | 1.5 - 25 mm <sup>2</sup>  |
| Packs of                           | 3 pc(s).  |
| Net weight                         | 0.975 kg  |
| Gross weight                       | 1.04 kg   |
| Copper weight (kg per piece)       | 0.066   |
| Customs tariff number              | 85369095  |
| ETIM 9                             | EC001046  |
| ECLASS 8.0                         | 27371402  |
| Product description                | SV Bus-mounting fuse base, D-Switch, 63 A, 400 V, 3-pole, round conductor connection 1,5-25 mm <sup>2</sup> |

# Approvals

Explanations

Declaration of conformity