

Rittal – The System.

Faster – better – everywhere.



SV 9340.550 OM adaptors

State: 03/07/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.550 - OM adaptors with spring terminals



Features

Model No.	SV 9340.550
Design	with spring terminals
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, 1 x TS 45C, PinBlock
Number of poles	3-pole
PinBlock	Yes
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 6 mm ²
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Packs of	1 pc(s).

Features

Net weight	0.238 kg
Gross weight	0.29 kg
Copper weight (kg per piece)	0.027
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 32 A, 690 V, 3-pole, tension spring clamp 1,5-6 mm ² , WH: 45x208 mm, support frame, PinBlock, support rail TS 45C

Approvals

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM adaptor 32 A

OM adaptor 32 A with tension spring clamp, 3-pole,
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 45 mm

Length: 208 mm

Support frame: 45 x 170 mm

Support frame support: -

PinBlock: yes

Connector outlet: -

Support rail: 1 with anti-slip guard

System:

Rittal RiLine60