

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.512

## RiLineX CB component adaptor

State: 27/05/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.512 - RiLineX CB component adaptor

This new product is currently unavailable. Alternatively, you can use the item number 9360.612.



## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | RX 9360.512   |
| Design                               | Easy Fix  |
| Benefits                             | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material                             | Polyamide (PA 6)<br>Fire protection corresponding to UL 94  |
| Colour                               | RAL 9005<br>RAL 35745   |
| Supply includes                      | 3 connection space covers   |
| IP protection category to IEC 60529  | IP 2XB  |
| Rated impulse withstand voltage Uimp | 8 kV  |
| Rated voltage                        | 690 V AC<br>600 V AC (UL)   |

# Features

|   |  |
|---|--|
| Rated insulation voltage Ui                     | 1,000 V  |
| Contamination level                             | 3  |
| Clamping area for laminated copper bars (W x H) | 15 x 6 mm  |
| Number of poles                                 | 3-pole   |
| Cable outlet                                    | Bottom   |
| Type of electrical connection                   | Screw M8   |
| To fit manufacturer (model)                     | ABB (S3 150, S3 225, S3, T3, T4, XT3, XT4, FE160, FE250)<br>Chint (NM8N-250, NM1-250H, NXM-250S, NXMS-250)<br>Eaton (LZMB2-A160, LZMB2-A250)<br>Fuji Electric (BW160_-3P, BW250_-3)<br>Hager (P250)<br>Himel (HDM3-160, HDM3-250, HDM3L-160, HDM3L-250)<br>Hyundai Electric (160, 250AF)<br>Legrand (DPX250, DPX <sup>3</sup> 250)<br>LS Electric (250AF, TS250)<br>Mitsubishi (NF125-SGV, NF160-SGV, NF250-SV)<br>OEZ (BD250)<br>Rockwell (140G-J0F3-D25)<br>Sassin (3SM8N-225, 3SM8L-225)<br>Schneider (EZC250H, NS100, NS160, NS250, NSX100, NSX160, NSX250, GV5)<br>Schrack (MC2)<br>Siemens (3VA20, 3VA21, 3VA22, 3VT2, 3RV1063, 3RV1363, 3RV1364, VL160/3VL2)<br>Terasaki (S160, S250, H250) |
| To fit busbar system                            | RiLineX<br>RiLine60  |
| Fundamental frequency                           | 50...60 Hz   |
| Ambient humidity (non-condensing)               | 10...90 %  |
| To fit busbars                                  | 15 x 5/10<br>20 x 5/10<br>30 x 5/10  |
| Operating temperature range                     | -25 °C...55 °C   |

# Features

---

|                               |   |
|-------------------------------|---|
| Storage temperature range     | -25 °C...75 °C  |
| Dimensions                    | Width: 105 mm<br>Height: 252 mm<br>Depth: 63 mm   |
| Packs of                      | 1 pc(s).  |
| Net weight                    | 1.7 kg  |
| Gross weight                  | 1.792 kg  |
| Copper weight (kg per piece)  | 0.608   |
| PCF per pack (cradle-to-gate) | 10.84   |
| Customs tariff number         | 85369095  |
| ETIM 9                        | EC001531  |
| Product description           | RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom. |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | UL + C-UL (listed)                           |
| Explanations | Declaration of conformity<br>PCF-declaration |