


Rittal – The System.

Faster – better – everywhere.




RX 9360.525

RiLineX CB component adaptor

State: 13/02/2026 (Source: rittal.com/com-en)

RX 9360.525 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 400 A) for 60 mm busbar systems. The device width is 145 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

Model No.	RX 9360.525
Design	Easy Fix
Benefits	<p>Direct mounting of moulded-case circuit-breakers (MCCBs) on the board</p> <p>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm</p> <p>Fast, simple pre-assembly of standard market switch types outside of the enclosure</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>
Colour	<p>RAL 9005</p> <p>RAL 35745</p>
Supply includes	3 terminal covers
IP protection category to IEC 60 529	IP 2XB
Rated impulse withstand voltage Uimp	12 kV

Features

Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage Ui	1,000 V
Overvoltage category	4
Contamination level	3
Clamping area for laminated copper bars (W x H)	29 x 6 mm
Number of poles	3-pole
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 145 mm Height: 325.8 mm
Packs of	1 pc(s).
Net weight	4
Gross weight	4.298
Copper weight (kg per piece)	1.652
Customs tariff number	85369095

Features

EAN 4028177997127

ETIM 9 EC001531

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity