


# Rittal – The System.

Faster – better – everywhere.



## RX 9360.760

### RiLineX component adaptor

State: 20/01/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

# RX 9360.760 - RiLineX component adaptor

RiLineX component adaptor (65 A, 3-pole, including connection cables) in width 54 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



## Features

Model No.	RX 9360.760
Design	With connection cable
Benefits	<p>For mounting equipment for top hat rail installation, e.g. motor starter</p> <p>Pre-assembled connection cable</p> <p>Simple clip locking for support rails</p> <p>Optional anti-slip guard</p> <p>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)</p> <p>Simple assembly</p> <p>Coordinated accessories reduce the number of different items required</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>
Colour	<p>RAL 9005</p> <p>RAL 35745</p>
Connection cables (AWG)	AWG 6
Rated current of round conductor	65 A
Rated current of round conductor (UL)	65 A

# Features

Electrical ratings UL (SCCR)	100 kA - 600 V, Fuse Class RK5 max. 60 A, JDDZ/7 20 kA - 600 V, circuit breaker max. 60 A, DIVQ/7 65 kA - 480 V, Combination Motor Controller max. 52 A, NKJH/7
Cable outlet	Top
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	130 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 54 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %

## Features

---

Packs of	4 pc(s).
Net weight	1.84
Gross weight	1.883
Copper weight (kg per piece)	0.145
Customs tariff number	85369095
EAN	4028177996991
ETIM 9	EC001531

---

## Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

---