

Rittal – The System.

Faster – better – everywhere.



SV 9345.015 Fuse holders

State: 12/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.015 - Fuse holders 31 A to 60 A

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

Features

| | |
|------------------------------------|--|
| Model No. | SV 9345.015 |
| Design | For category J fuse type |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Connection for round conductor | AWG 1 - 18 |
| Type of electrical connection | Box terminal |
| For fuse type (class) | J |
| Rated operating current max. | 30 A |
| Rated operating voltage | 600 V, 3~ |
| Fuse standard | UL 248-8 |
| Note | For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports) |
| Test specification | UL 4248-1 UL 4248-4 UL 4248-8 |
| Dimensions | Width: 108 mm Height: 115 mm |
| Connection of round conductors | 1.5 - 50 mm ² |
| To fit fuses | Diameter: 21 mm Length: 57 mm |
| Voltage range for indicator lights | 110 - 600 V |
| Electrical ratings UL (SCCR) | 200 kA - 600 V, Fuse Class J max. 30 A, JDDZ/7 |

Features

| | |
|-------------------------------|--|
| Number of poles | 3-pole |
| Round conductor cross-section | 1.5 - 50 mm ² |
| Packs of | 2 pc(s). |
| Net weight | 0.84 kg |
| Gross weight | 0.966 kg |
| Copper weight (kg per piece) | 0.072 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001644 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Fuseholder, Class J, 30 A, 600 V, 3-pole, (60 mm) |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |