


Rittal – The System.

Faster – better – everywhere.



SV 9661.240

PE/PEN combination angle E-Cu

State: 14/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9661.240 - PE/PEN combination angle E-Cu for PE/PEN combinations

The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.

Features

Model No.	SV 9661.240
Product description	The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.
Benefits	Thanks to the pre-assembled combination angles, baying brackets and busbars customised to match the enclosure width, assembly is time-saving with cost reduction
Applications	Form 2-4
Material	E-Cu
Supply includes	Assembly parts
Approved short-circuit current capability	I _{cw} 60kA, 1 sec.
To fit busbars	Busbar E-Cu with integral punchings
OUT_CROSS_SECTION_COL_SM	40 - 10 mm
To fit busbars	Width: 40, 80 Height: 10, 10 mm
Packs of	4 pc(s).
Net weight	2.2 kg
Gross weight	2.356 kg
Copper weight (kg per piece)	0.44
Customs tariff number	74198090
ETIM 9	EC000329
ECLASS 8.0	27400605

Features

Product description

SV PE/PEN combination angle E-Cu, WH: 40x10 mm, L: 135 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK