Rittal – The System.

Faster – better – everywhere.



# SV 9676.747
# Connection plate

State: 03/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9676.747 - Connection plate for laminated copper bars

For the connection of laminated flat copper bars.

## Features

| | |
|---|---|
| Model No. | SV 9676.747 |
| Product description | For connecting laminated copper bars to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness. |
| Material | Connection plate: E-Cu<br>Thrust piece: Stainless steel<br>Busbar claw: Stainless steel |
| Supply includes | Assembly parts (excluding screws) |
| Assembly instruction | The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply.<br>Busbar claw with threaded insert M10 |
| Bars per conductor | 2 |
| Mounting dimensions | 50 mm |
| Clamping area for laminated copper bars (W x H) | 32 x 20 mm |
| To fit laminated copper bars | Qty.: 2<br>with no. of membranes: 10<br>with membrane width: 32 mm<br>with membrane thickness: 1 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.34 kg |
| Gross weight | 0.346 kg |
| Copper weight (kg per piece) | 0.13 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002270 |
| ECLASS 8.0 | 27400613 |

© Rittal 2026

# Features

| | |
|---|---|
| Product description | SV Connection plate, clamping area WH: 32x20 mm, (Flat-PLS) |

# Approvals

| | |
|---|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |