

Rittal – The System.

Faster – better – everywhere.



SV 9676.748 Connection plate

State: 25/08/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.748 - Connection plate for laminated copper bars

For the connection of laminated flat copper bars.

Features

Model No.	SV 9676.748
Product description	For connecting laminated copper bars to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness.
Material	Connection plate: E-Cu Thrust piece: Stainless steel Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Assembly instruction	The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply. Busbar claw with threaded insert M10
Number of bars per conductor	2
Mounting dimensions	50 mm
Clamping area for laminated copper bars (W x H)	63 x 20 mm
To fit laminated copper bars	Qty.: 2 with no. of membranes: 10 with membrane width: 63 mm with membrane thickness: 1 mm
Packs of	1 pc(s).
Net weight	0.47
Gross weight	0.478
Copper weight (kg per piece)	0.19
Customs tariff number	73269098
EAN	4028177625563
ETIM 9	EC002270

Features

ECLASS 8.0	27400613
------------	----------

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---