Rittal – The System.

Faster – better – everywhere.



# SV 9635.100

# Circuit-breaker component adaptor

State: 04/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9635.100 - Circuit-breaker component adaptor 3-pole

For mechanical attachment and direct contacting of circuit-breakers on the board.

## Features

| | |
|---|---|
| Model No. | SV 9635.100 |
| Function principle | For mechanical attachment and direct contacting of circuit-breakers on the board<br>Circuit-breaker is fitted using variably adjustable fixing points (M4) |
| Material | Polyamide<br>Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Note | Consider the mounting distance of the circuit-breaker when selecting the circuit-breaker component adaptor<br>Depending on the circuit-breaker used, there may be a reduction in output<br>The technical data may vary for UL applications |
| Rated current max. | 160 A |
| Rated operating voltage | 600 V (DC), 3~<br>690 V (AC), 3~ |
| Number of poles | 3-pole |
| Dimensions | Width: 90 mm<br>Height: 160 mm<br>Depth: 45 mm |
| Distance between fixing points | 25 mm |
| Cable outlet | Top/bottom |
| To fit manufacturer (model) | ABB (XT1)<br>Allen Bradley (140G-G)<br>Siemens (3VA10, 3VA11, 3VA51) |
| Packs of | 1 pc(s). |
| Net weight | 0.58 kg |
| Gross weight | 0.582 kg |

© Rittal 2026

# Features

| | |
|---|---|
| Copper weight (kg per piece) | 0.276 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV CB component adaptor160 A, 690 V (AC), 600 V (DC), 3-pole WH: 90 x 160 mm, mounting distance 25 mm |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |